



G GREENLEE

ELECTRIC BENDERS

Intellibender® Electric Conduit Bender





A PRODUCT VIDEO IS AVAILABLE, SCAN THIS QR **CODE OR VISIT:**

www.youtube.com/GreenleeDEMO











Switching the 855GX between vertical and horizontal bending configurations is simple and can be done in seconds with its unique pivoting cylinder.

• The 855GX is Greenlee's most advanced programmable bender

SIMPLE. READY TO BEND IN 2 STEPS







ORIENT SHOES (2) SELECT ANGLE -

PRODUCTIVE. 4X FASTER SETUP' **ACCURATE. LESS SCRAP & REWORK**

Type of Conduit	Every 100 Pieces Not Scrapped ²
2" Rigid	\$4382.80
2" EMT	\$1674.00

RELIABLE. MORE UPTIME TO BEND

SPECIFICATIONS

Amperage Rating 20 AMP GFCI-Protected Receptacle **Power Source**

Capacity 1/2 - 2.000 IN Rigid/EMT/IMC Conduit

Weight 532 lbs.

CAT. NO.	UPC NO.	DESCRIPTION	
855GX	12579	Bender, Electric Conduit - Programmable (120 VAC, 20A)	
12582	12582	Shoe Group, 1/2" - 2" PVC Coated Rigid (855GX)	

CAT NO.	SHOE GROUP	855GX
	5.1.1.2 S.1.1.2.1.	
12581	1/2"- 2" PVC Coated	√ 1
37279	1/2"- 2" PVC Coated	
12582	1/2"- 2" PVC Coated	1
12302	1/2 - 2 1 VO GOALEU	V
01700	1/2"- 2" PVC Coated	√ 1

¹ Need 13855 support roller assembly to bend 1/2"- 1-1/4" PVC coatd rigid on 855GX.


BENDING RADII COMBO SHOE GROUP

OLIOF OIZE	INOLIEO	
SHOE SIZE	INCHES	mm
1/2" EMT	4-5/16"	109.5
1/2" IMC/Rigid	4-1/4"	108.0
3/4" EMT	5-1/2"	139.7
3/4" IMC/Rigid	5-7/16"	138.1
1" EMT	7"	177.8
1" IMC/Rigid	6-15/16"	176.2
1-1/4" EMT	8-13/16"	223.8
1-1/4" IMC/Rigid	8-3/4"	222.3
1-1/2" EMT	8-3/8"	212.7
2" EMT	9-1/4"	235.0
2" IMC/Rigid	9"	228.6

¹Speed claims based on timed 4-bend saddle comparisons between the 855GX and other similar benders. ²Claims based on list price of 10' long EMT and Rigid conduit.


³Solid-state electronics system rated for 1,000,000+ bends.

1/2" – 2" Rigid Shoe Group



KEY	CAT. NO.	UPC NO.	DESCRIPTION
	28007	28007	1/2" - 2" Rigid Shoe Group
Α	00571	00571	1/2" through 1-1/4" Rigid/IMC Bending Shoe
В	00936	00936	1/2" through 1-1/4" Support Roller
С	17937	17937	1-1/2" through 2" Rigid Bending Shoe
D	17984	17984	1-1/2" through 2" Support Roller

1/2" - 2" EMT Shoe Group



KEY	CAT. NO.	UPC NO.	DESCRIPTION
	23802	23802	1/2" - 2" EMT Shoe Group
Α	17944	17944	1/2" through 1-1/4" EMT Bending Shoe
В	17986	17986	1/2" through 1-1/4" Support Roller
С	23499	23499	1-1/2" EMT Bending Shoe
D	23505	23505	2" EMT Bending Shoe
Ε	23541	23541	1-1/2" through 2" Roller Support Unit
	1723	23818	Metal Storage Box
	12580	12580	Shoe Group. 1/2"-2" EMT/Rigid Combo (555 Series)

1-1/2" - 2" IMC Shoe Group



KE	Y	CAT. NO.	UPC NO.	DESCRIPTION
		26330	26330	1-1/2" - 2" IMC Shoe Group
A	A	25263	25263	1-1/2" IMC Bending Shoe
В	3	25268	25268	2" IMC Bending Shoe
C)	25273	25273	1-1/2" through 2" Roller Support Unit
		1723	23818	Metal Storage Box

40ML PVC Coated Rigid 1/2" – 2" Shoe Group



KEY	CAT. NO.	UPC NO.	DESCRIPTION
	37279	37279	40 ml PVC Coated Rigid 1/2" - 2" Shoe Group
Α	00946	00946	1/2" through 1-1/4" Roller Support
В	00573	00573	1/2" through 1-1/4" Shoe
С	37281	37281	1-1/2" and 2" Shoe
D	37282	37282	1-1/2" through 2" Roller Support
	1723	23818	Metal Storage Box
	12581	12581	Shoe Group, 1/2" - 2" PVC Coated Rigid (555 Series)
	12582	12582	Shoe Group, 1/2" - 2" PVC Coated Rigid (855GX)

To use the PVC Shoe Group with 555 SB and 555 SBR benders Adapter Set 32391 is required.